

Product Id	Model No.	Classification
PIA5OJ35	FBY12L835-(UNV,347,480)	Premium
PBSXNKD0	FBY12L835-(UNV,347,480)-LCA	standard
PNHXP1NM	FBY12L835-(UNV,347,480)-LCR	standard
POCIHIR2	FBY12L835-(UNV,347,480)-LFA	standard
P3SCCJHO	FBY12L835-(UNV,347,480)-LFR	standard
POYV923N	FBY12L835-UNV-(MD360,MD360D,BSL10LST,SWIDT)	standard
PIMJLME3	FBY12L835-UNV-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
POTHM5EU	FBY12L835-UNV-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PQVF2QW9	FBY12L835-UNV-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PW0UOWZU	FBY12L835-UNV-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PTROXXST	FBY12L840-(UNV,347,480)	Premium
PTKIWD2P	FBY12L840-(UNV,347,480)-LCA	Premium
PDJVGXVX	FBY12L840-(UNV,347,480)-LCR	standard
PC9XHMZK	FBY12L840-(UNV,347,480)-LFA	standard
PFGP0WM5	FBY12L840-(UNV,347,480)-LFR	standard
P74X1Z79	FBY12L840-UNV-(MD360,MD360D,BSL10LST,SWIDT)	Premium
P113G5SD	FBY12L840-UNV-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
P8FHURW6	FBY12L840-UNV-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PH4YSH8B	FBY12L840-UNV-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PN77K9TB	FBY12L840-UNV-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PUJ45NEW	FBY12L850-(UNV,347,480)	Premium
PIDGWX0G	FBY12L850-(UNV,347,480)-LCA	Premium
PZX358ZP	FBY12L850-(UNV,347,480)-LCR	standard
PKRTT1WJ	FBY12L850-(UNV,347,480)-LFA	standard
PX8SJK8	FBY12L850-(UNV,347,480)-LFR	standard
POHRZZH3	FBY12L850-UNV-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PCTRDCGF	FBY12L850-UNV-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PAZ7TPDF	FBY12L850-UNV-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PUMAW3NN	FBY12L850-UNV-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PCLRWCB3	FBY12L850-UNV-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PUVURR19	FBY18L835-(UNV,347,480)	Premium
PNX91ZL2	FBY18L835-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	standard
P90FJY38	FBY18L835-(UNV,347,480)-LCA	Premium
P083AF8T	FBY18L835-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PYHKJE1K	FBY18L835-(UNV,347,480)-LCR	standard
PKHJROJO	FBY18L835-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PZC7BGXR	FBY18L835-(UNV,347,480)-LFA	standard
PM8HA7V4	FBY18L835-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PEPHRTCD	FBY18L835-(UNV,347,480)-LFR	standard
POGUDJII	FBY18L835-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PB6089U5	FBY18L840-(UNV,347,480)	Premium
PLIFTATZ	FBY18L840-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	standard
PHKO7A0F	FBY18L840-(UNV,347,480)-LCA	Premium
PQIGPRR6	FBY18L840-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PVVE1GNN	FBY18L840-(UNV,347,480)-LCR	standard
P51CZUJX	FBY18L840-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PSQI9J2A	FBY18L840-(UNV,347,480)-LFA	standard
PASTG4XT	FBY18L840-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PAQGZKBA	FBY18L840-(UNV,347,480)-LFR	standard
PQPR1YIQ	FBY18L840-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PY8IPZZ7	FBY18L850-(UNV,347,480)	Premium
PQRQ4HDK	FBY18L850-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	standard
PTMJGVVX	FBY18L850-(UNV,347,480)-LCA	Premium

Product Id	Model No.	Classification
PB8HP9VI	FBY18L850-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PUDUJN2Z	FBY18L850-(UNV,347,480)-LCR	standard
PMDU3JKB	FBY18L850-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PH2984UY	FBY18L850-(UNV,347,480)-LFA	standard
PGWKYYLG	FBY18L850-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
P3E8KT81	FBY18L850-(UNV,347,480)-LFR	standard
P4FUNOS1	FBY18L850-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PV8J2ZTO	FBY24L835-(UNV,347,480)	Premium
P96UHV17	FBY24L835-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	standard
PTIGM5O5	FBY24L835-(UNV,347,480)-LCA	standard
PFKK0394	FBY24L835-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PQ0FI497	FBY24L835-(UNV,347,480)-LCR	standard
P2JLC562	FBY24L835-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PYPFBH05	FBY24L835-(UNV,347,480)-LFA	standard
PQ49FORZ	FBY24L835-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
P6UXGVOL	FBY24L835-(UNV,347,480)-LFR	standard
P2LOGH73	FBY24L835-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PYLFJK6U	FBY24L840-(UNV,347,480)	Premium
PQQXYLDK	FBY24L840-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PPI7T1GR	FBY24L840-(UNV,347,480)-LCA	Premium
P8JSCTAW	FBY24L840-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PKHNXETN	FBY24L840-(UNV,347,480)-LCR	standard
PEQXK28P	FBY24L840-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PH2HPELQ	FBY24L840-(UNV,347,480)-LFA	standard
PB3PLKNH	FBY24L840-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
POHYCGPQ	FBY24L840-(UNV,347,480)-LFR	standard
PIE6VAAU	FBY24L840-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PMQUZS4L	FBY24L850-(UNV,347,480)	Premium
P4EV6OV9	FBY24L850-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PWDNKMUN	FBY24L850-(UNV,347,480)-LCA	Premium
P2BEYNG6	FBY24L850-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PSJP546W	FBY24L850-(UNV,347,480)-LCR	standard
PQF2RQNV	FBY24L850-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PZ190U9B	FBY24L850-(UNV,347,480)-LFA	standard
P6K46Q8W	FBY24L850-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PFG1VWTT	FBY24L850-(UNV,347,480)-LFR	standard
PMJRW5BH	FBY24L850-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
P9YEO07Y	FBY30L835-(UNV,347,480)	Premium
PU32WUB1	FBY30L835-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PY7Y2ZYM	FBY30L835-(UNV,347,480)-LCA	Premium
PWK6GBVV	FBY30L835-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PA9NVSH1	FBY30L835-(UNV,347,480)-LCR	standard
P83MNOQ3	FBY30L835-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PAIDWYRU	FBY30L835-(UNV,347,480)-LFA	standard
PRZYIDDU	FBY30L835-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PZIT5GN1	FBY30L835-(UNV,347,480)-LFR	standard
PHNUGXVK	FBY30L835-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
P66UVSWZ	FBY30L840-(UNV,347,480)	Premium
PNS4AZDC	FBY30L840-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PB89N1S4	FBY30L840-(UNV,347,480)-LCA	Premium
P75ROPDU	FBY30L840-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PG233HQS	FBY30L840-(UNV,347,480)-LCR	standard
POFF71MI	FBY30L840-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard

3/4/2019

Information as of this date. Please check the DLC QPL for confirmation (www.designlights.org/QPL).

Product Id	Model No.	Classification
PPGK2XTY	FBY30L840-(UNV,347,480)-LFA	Premium
PFR85UTY	FBY30L840-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PZRAHBVJ	FBY30L840-(UNV,347,480)-LFR	standard
PIXT2E7J	FBY30L840-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PW0866VE	FBY30L850-(UNV,347,480)	Premium
PISOAR2Z	FBY30L850-(UNV,347,480)-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PFEGPYR4	FBY30L850-(UNV,347,480)-LCA	Premium
POJLS333	FBY30L850-(UNV,347,480)-LCA-(MD360,MD360D,BSL10LST,SWIDT)	Premium
PJTZC23J	FBY30L850-(UNV,347,480)-LCR	standard
PY4FCXRR	FBY30L850-(UNV,347,480)-LCR-(MD360,MD360D,BSL10LST,SWIDT)	standard
PJVXBVPI	FBY30L850-(UNV,347,480)-LFA	Premium
PSZT8H1H	FBY30L850-(UNV,347,480)-LFA-(MD360,MD360D,BSL10LST,SWIDT)	standard
PEJISYHZ	FBY30L850-(UNV,347,480)-LFR	standard
PJ5GG898	FBY30L850-(UNV,347,480)-LFR-(MD360,MD360D,BSL10LST,SWIDT)	standard