

Product Id	Model No.	Classification
P6SYW1ES	FSS220L830-UNV-DIM-( _LSXR10)	standard
PCKM7D5F	FSS220L835-UNV-DIM-( _LSXR10)	standard
PU26C9EC	FSS220L840-347-DIM-( _LSXR10)	standard
P81A9ZVK	FSS220L840-UNV-DIM-( _LSXR10)	standard
PC926MF4	FSS220L850-347-DIM-( _LSXR10)	standard
PN2SJA4	FSS220L850-UNV-DIM-( _LSXR10)	standard
PNKWMAA4	FSS230L830-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PZ2U2AQZ	FSS230L835-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PMKZSE9N	FSS230L835-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P1JDNPSF	FSS230L840-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PT5YCYN6	FSS230L840-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PS236GRN	FSS230L850-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PRK18DHA	FSS230L850-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PHHDK2D5	FSS330L830-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PR8HMY7V	FSS330L835-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PS336FZB	FSS330L840-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PBWD1TGH	FSS330L840-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PA9BXNMA	FSS330L850-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PD6GS6UT	FSS330L850-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P4SMQB5H	FSS430L830-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PV4Z1Y5Y	FSS430L830-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PM7U9E5M	FSS430L835-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PBJ6B7XT	FSS430L835-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PXKHS4C0	FSS430L840-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PB30RVG0	FSS430L840-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PL01BELE	FSS430L850-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PY0UELTU	FSS430L850-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PEYEJE2	FSS440L830-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PMTXRMQQ	FSS440L830-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PQMPVP3M	FSS440L830-UNV-DIM-EMLED	standard
PKFR4JW9	FSS440L835-(UNV347)-DIM-EMLED	standard
PXBDE6GE	FSS440L835-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PCB52PCA	FSS440L835-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PR3Y8NQS	FSS440L840-(UNV347)-DIM-EMLED	standard
PXXB9TYH	FSS440L840-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PGC3XP1W	FSS440L840-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P9BD9MQ9	FSS440L850-(UNV347)-DIM-EMLED	standard
PF81EFN6	FSS440L850-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PWAUN7WE	FSS440L850-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PWRQWFCT	FSS455L830-(UNV347)-DIM-EMLED	standard
PBHKSESS	FSS455L830-(UNV347)-DIM-EMLED	standard
PP266GSV	FSS455L830-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PBCCHJK3	FSS455L830-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PPCFNU64	FSS455L830-UNV-(DIMXDIMSDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P9X3687Q	FSS455L830-UNV-(DIMXDIMSDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P8P9NZK2	FSS455L835-(UNV347)-DIM-EMLED	standard
P8Q2DZ9B	FSS455L835-(UNV347)-DIM-EMLED	standard
PJGNBJVQ	FSS455L835-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P1U8AATG	FSS455L835-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PP59TP3Y	FSS455L835-UNV-(DIMXDIMSDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PZK4MKNS	FSS455L835-UNV-(DIMXDIMSDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P2MBHUMX	FSS455L840-(UNV347)-DIM-EMLED	standard
P34NUE22	FSS455L840-(UNV347)-DIM-EMLED	standard

Product Id	Model No.	Classification
P34SG8SZ	FSS455L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P617ZTJV	FSS455L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P1W6MKZ9	FSS455L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PF5H96K7	FSS455L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PRWMQCU7	FSS455L850-(UNV347)-DIM-EMLED	standard
PHCGCCYN	FSS455L850-(UNV347)-DIM-EMLED	standard
PBYTSDRY	FSS455L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P5KDQF1U	FSS455L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PG76F9NC	FSS455L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P6ZFAZNX	FSS455L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PC8EF9D8	FSS470L830-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PWQUVHK5	FSS470L830-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P1S4CATG	FSS470L830-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PRRN1M4F	FSS470L830-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P6ZMWNM5	FSS470L830-UNV-DIM-EMLED	standard
P7N47758	FSS470L830-UNV-DIM-EMLED	standard
P1ERBCPQ	FSS470L835-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P1Z3S21S	FSS470L835-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PCPHP37U	FSS470L835-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PUN222FK	FSS470L835-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PRBD8562	FSS470L835-UNV-DIM-EMLED	standard
PJ3JNTRR	FSS470L835-UNV-DIM-EMLED	standard
PN6S1MTP	FSS470L840-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PHTSE29F	FSS470L840-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PJ876F3M	FSS470L840-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PM9HFWVU	FSS470L840-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PCENT7X5	FSS470L840-UNV-DIM-EMLED	standard
PDCKHN7N	FSS470L840-UNV-DIM-EMLED	standard
PKZ8C8FG	FSS470L850-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P7BH45P4	FSS470L850-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PHMZGPRS	FSS470L850-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PJDTE6QX	FSS470L850-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PPTWFV1S	FSS470L850-UNV-DIM-EMLED	standard
PQMTXDHN	FSS470L850-UNV-DIM-EMLED	standard
PV4FGCC2	FSS8110L830-(UNV347)-DIM-EMLED	standard
PB3Z4V63	FSS8110L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PDCJSMZH	FSS8110L830-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PVSMGMPE	FSS8110L835-(UNV347)-DIM-EMLED	standard
P5V7RU5A	FSS8110L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P1QT37RS	FSS8110L835-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PX2ZQH2F	FSS8110L840-(UNV347)-DIM-EMLED	standard
PWV4383N	FSS8110L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PC5EKZDZ	FSS8110L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PVP SHN3H	FSS8110L850-(UNV347)-DIM-EMLED	standard
PN5A2ZWY	FSS8110L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PH2NBB3A	FSS8110L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P1X3CX95	FSS8140L830-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PACYWCX7	FSS8140L830-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PC3JYKYH	FSS8140L830-UNV-DIM-EMLED	standard
PNGF597G	FSS8140L835-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PZ4BHFZC	FSS8140L835-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PYYR9FDX	FSS8140L835-UNV-DIM-EMLED	standard
PWHUCD9K	FSS8140L840-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard

3/4/2019

Information as of this date. Please check the DLC QPL for confirmation ([www.designlights.org/QPL](http://www.designlights.org/QPL)).

Product Id	Model No.	Classification
PGHYCX4S	FSS8140L840-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PJXN684N	FSS8140L840-UNV-DIM-EMLED	standard
PD4ZDVVS	FSS8140L850-347-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PQWGXBP	FSS8140L850-UNV-DIM-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PWNFT6V2	FSS8140L850-UNV-DIM-EMLED	standard
PZSP63BD	FSS860L830-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PY8IXS66	FSS860L830-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P5P422ZO	FSS860L830-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PI9EZ5QG	FSS860L830-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PVGWGWGE	FSS860L835-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PM9G8BKK	FSS860L835-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P6PS4QL5	FSS860L835-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PSNOFUKX	FSS860L835-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PJW7FWI5	FSS860L840-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P81AA83I	FSS860L840-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PCRYK706	FSS860L840-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P22PSYUS	FSS860L840-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P05UZ1YQ	FSS860L850-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P3Y5D0AG	FSS860L850-347-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PQG8FCOF	FSS860L850-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
PIKMPAL4	FSS860L850-UNV-DIM-( _LSXR10, DAYOCC, SWZDT, IAP)	standard
P93ZT9QD	FSS880L830-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PFKNC2KM	FSS880L830-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PXU9GDB7	FSS880L830-UNV-DIM-EMLED	standard
PANDXEFM	FSS880L835-(UNV347)-DIM-EMLED	standard
PUZC2F6C	FSS880L835-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P3UB139I	FSS880L835-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P2KM8MVQ	FSS880L840-(UNV347)-DIM-EMLED	standard
P9W9SYUN	FSS880L840-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P7HV92D1	FSS880L840-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PKR2B5AV	FSS880L850-(UNV347)-DIM-EMLED	standard
PG5U86W6	FSS880L850-347-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
PDX13UAX	FSS880L850-UNV-(DIMXDIM)-( _LSXR10 DAYOCC, SWZDT, IAP)	standard
P5UKPWRT	FSSEZ440L835-UNV	standard
PVX217M4	FSSEZ440L840-UNV	standard