

3/4/2019

Information as of this date. Please check the DLC QPL for confirmation ([www.designlights.org/QPL](http://www.designlights.org/QPL)).

Product Id	Model No.	Classification
PU298VTE	HBY12L835-(UNV,347,480)-A-xx	Premium
PRO2EYXO	HBY12L835-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PM0VNSUT	HBY12L835-(UNV,347,480)-M-xx	Premium
PG1LVQ3M	HBY12L835-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PGC5D5OF	HBY12L835-(UNV,347,480)-N-xx	Premium
P4MCWNEX	HBY12L835-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
P5TQL4UE	HBY12L835-(UNV,347,480)-W-xx	Premium
PZ37BMDE	HBY12L835-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
POG6OKQX	HBY12L840-(UNV,347,480)-A-xx	Premium
PBG8B2V0	HBY12L840-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PRLXU0TO	HBY12L840-(UNV,347,480)-M-xx	Premium
PZU9P0ZV	HBY12L840-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
P3CIE2A5	HBY12L840-(UNV,347,480)-N-xx	Premium
PIQ4T7J7	HBY12L840-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PT3HI6UH	HBY12L840-(UNV,347,480)-W-xx	Premium
P5R0TE68	HBY12L840-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
P44JUH2J	HBY12L850-(UNV,347,480)-A-xx	Premium
POQW91CS	HBY12L850-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
P4LXH38O	HBY12L850-(UNV,347,480)-M-xx	Premium
PV9Q40S2	HBY12L850-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PYEM3ARS	HBY12L850-(UNV,347,480)-N-xx	Premium
PLDW4Y4H	HBY12L850-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PZ9W31S1	HBY12L850-(UNV,347,480)-W-xx	Premium
P7WMNCPW	HBY12L850-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PY42POC1	HBY18L835-(UNV,347,480)-A-xx	Premium
PBVOF64W	HBY18L835-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PMC31R5K	HBY18L835-(UNV,347,480)-M-xx	Premium
PXJ3UP5N	HBY18L835-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PEQN6QW5	HBY18L835-(UNV,347,480)-N-xx	Premium
PZJTPTHA	HBY18L835-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PTOWOBSW	HBY18L835-(UNV,347,480)-W-xx	standard
PHE3PST5	HBY18L835-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
P3D2W05S	HBY18L840-(UNV,347,480)-A-xx	Premium
P3TMYIJ7	HBY18L840-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PME22CTK	HBY18L840-(UNV,347,480)-M-xx	Premium
PGZJHCQD	HBY18L840-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PYOV4EV6	HBY18L840-(UNV,347,480)-N-xx	Premium
P6TNACFZ	HBY18L840-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PVOLPJ3N	HBY18L840-(UNV,347,480)-W-xx	Premium
PBQ9VLDF	HBY18L840-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PUGYYHNX	HBY18L850-(UNV,347,480)-A-xx	Premium
P753XTK2	HBY18L850-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PK3HI4QX	HBY18L850-(UNV,347,480)-M-xx	Premium
PRFX1290	HBY18L850-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PDSQWSS0	HBY18L850-(UNV,347,480)-N-xx	Premium
PSQHNUJ2	HBY18L850-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
P8GAL1NU	HBY18L850-(UNV,347,480)-W-xx	Premium
PCNK8GA2	HBY18L850-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	Premium
PMGQZM23	HBY24L835-(UNV,347,480)-A-xx	standard
PK72PNJ4	HBY24L835-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
P59HE2KZ	HBY24L835-(UNV,347,480)-M-xx	standard
PEO3MVZV	HBY24L835-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PKWX4OLF	HBY24L835-(UNV,347,480)-N-xx	standard

Product Id	Model No.	Classification
PJLOTK1B	HBY24L835-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PC85H51E	HBY24L835-(UNV,347,480)-W-xx	standard
P3EJE4CC	HBY24L835-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PPG2PA57	HBY24L840-(UNV,347,480)-A-xx	standard
PONPLOI6	HBY24L840-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PN6KH70I	HBY24L840-(UNV,347,480)-M-xx	standard
PI1NGYBU	HBY24L840-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PVXVUYJ8	HBY24L840-(UNV,347,480)-N-xx	standard
P5IUUK3SF	HBY24L840-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PO612BN0	HBY24L840-(UNV,347,480)-W-xx	standard
POYFTANL	HBY24L840-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PDEMFN34	HBY24L850-(UNV,347,480)-A-xx	standard
PWE7VDTN	HBY24L850-(UNV,347,480)-A-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PSNDUGH1	HBY24L850-(UNV,347,480)-M-xx	Premium
PU1XH1Y7	HBY24L850-(UNV,347,480)-M-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PD119CGH	HBY24L850-(UNV,347,480)-N-xx	Premium
PIOH3C9G	HBY24L850-(UNV,347,480)-N-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PSFI4J2Y	HBY24L850-(UNV,347,480)-W-xx	standard
PVRAP8ZD	HBY24L850-(UNV,347,480)-W-xx-(MD360W,MD360WD,SWIDT,BSL10LST)	standard
PSA1Z1Y4	HBY30L835-UNV-A-xx	standard
PPOLHTWY	HBY30L835-UNV-A-xx-(MD360W,MD360WD,SWIDT)	standard
PGV1VKBB	HBY30L835-UNV-M-xx	standard
P041LIL6	HBY30L835-UNV-M-xx-(MD360W,MD360WD,SWIDT)	standard
PLE4A7US	HBY30L835-UNV-N-xx	standard
PJGA6YJP	HBY30L835-UNV-N-xx-(MD360W,MD360WD,SWIDT)	standard
PC078XYT	HBY30L835-UNV-W-xx	standard
PTRG8IGZ	HBY30L835-UNV-W-xx-(MD360W,MD360WD,SWIDT)	standard
PMHGZFXD	HBY30L840-UNV-A-xx	Premium
PR3X0VEE	HBY30L840-UNV-A-xx-(MD360W,MD360WD,SWIDT)	Premium
PRPWYIGB	HBY30L840-UNV-M-xx	Premium
POQBR2J3	HBY30L840-UNV-M-xx-(MD360W,MD360WD,SWIDT)	Premium
P2BCMIJ	HBY30L840-UNV-N-xx	Premium
P42CUY5W	HBY30L840-UNV-N-xx-(MD360W,MD360WD,SWIDT)	Premium
PUPE5AW7	HBY30L840-UNV-W-xx	Premium
PEE8K5YW	HBY30L840-UNV-W-xx-(MD360W,MD360WD,SWIDT)	Premium
PHVT3UYY	HBY30L850-UNV-A-xx	Premium
P6UA52ZF	HBY30L850-UNV-A-xx-(MD360W,MD360WD,SWIDT)	Premium
P3AZY7L2	HBY30L850-UNV-M-xx	Premium
PZ15UNB6	HBY30L850-UNV-M-xx-(MD360W,MD360WD,SWIDT)	Premium
P5B168L7	HBY30L850-UNV-N-xx	Premium
PQIF5ZBU	HBY30L850-UNV-N-xx-(MD360W,MD360WD,SWIDT)	Premium
P65YT0DL	HBY30L850-UNV-W-xx	Premium
PPN35BBF	HBY30L850-UNV-W-xx-(MD360W,MD360WD,SWIDT)	Premium
PP0E8U6N	HBY36L835-UNV-A-xx	standard
P1JWMGTK	HBY36L835-UNV-A-xx-(MD360W,MD360WD,SWIDT)	standard
P5WVY6A	HBY36L835-UNV-M-xx	standard
PVYP9JUP	HBY36L835-UNV-M-xx-(MD360W,MD360WD,SWIDT)	standard
PVGFICLR	HBY36L835-UNV-N-xx	standard
PDMFKN7O	HBY36L835-UNV-N-xx-(MD360W,MD360WD,SWIDT)	standard
POVJGB9L	HBY36L835-UNV-W-xx	standard
PCMM8GKV	HBY36L835-UNV-W-xx-(MD360W,MD360WD,SWIDT)	standard
P4PROB4W	HBY36L840-UNV-A-xx	standard
P2IHDE3P	HBY36L840-UNV-A-xx-(MD360W,MD360WD,SWIDT)	standard

3/4/2019

Information as of this date. Please check the DLC QPL for confirmation ([www.designlights.org/QPL](http://www.designlights.org/QPL)).

<b>Product Id</b>	<b>Model No.</b>	<b>Classification</b>
P02Y1G0O	HBY36L840-UNV-M-xx	standard
PS1VL3EB	HBY36L840-UNV-M-xx-(MD360W,MD360WD,SWIDT)	standard
PX7WTR0S	HBY36L840-UNV-N-xx	standard
PATOL0VV	HBY36L840-UNV-N-xx-(MD360W,MD360WD,SWIDT)	standard
PCJ8QR91	HBY36L840-UNV-W-xx	standard
PD4IOVHX	HBY36L840-UNV-W-xx-(MD360W,MD360WD,SWIDT)	standard
PENBU5YE	HBY36L850-UNV-A-xx	Premium
P1X4Y92P	HBY36L850-UNV-A-xx-(MD360W,MD360WD,SWIDT)	standard
P1G72U33	HBY36L850-UNV-M-xx	standard
P6HCG65K	HBY36L850-UNV-M-xx-(MD360W,MD360WD,SWIDT)	standard
POU63L3W	HBY36L850-UNV-N-xx	standard
PYIX0FHR	HBY36L850-UNV-N-xx-(MD360W,MD360WD,SWIDT)	standard
PD13YDJC	HBY36L850-UNV-W-xx	standard
PMDVPUZG	HBY36L850-UNV-W-xx-(MD360W,MD360WD,SWIDT)	standard